

APCO Coatings (NZ) Limited

14 Ron Driver Place
East Tamaki
PO Box 58849 Botany
Manukau 2163
0800 BUY APCO



Technical Data Sheet Product No: EZT100

ezi•cover Ultra Low Sheen Acrylic

Description:

Ezicover Ultra Low Sheen Acrylic is a professional quality, extremely versatile, Interior finish. Excellent flow and leveling properties. Suitable for Walls & Ceilings in living areas.

Features and Benefits:

- Subtle, near flat sheen
- Ideal for living areas of high illumination
- Low splatter formula
- Easy Application
- Excellent adhesion to primed & properly prepared painted surfaces.

Limitations:

- Do not apply when the ambient temperature is below 10°C or the surface temperature is above 40°C.
- Being thermoplastic, the film is sensitive towards alcohol & aromatic hydrocarbons.
- Not recommended for wet areas.

Technical Data:

Resin Type:	100% Acrylic Emulsion
Pigmentation:	Inorganic pigments and extenders
Solvents:	Water
Colour:	White & tint bases
Gloss Level:	3 – 5%
Density:	1.48 Kgs/ Litre
Dry-Time:	30 mins Touch dry, 2 hour sand and overcoat. Cooler temperatures, higher film thickness or high humidity will require longer drying times.
Coverage:	12 m ² per litre
No. of coats:	Two
Flash Point:	None
Thinner:	Water
VOC:	27 g/l

APCO Coatings (NZ) Limited

14 Ron Driver Place
East Tamaki
PO Box 58849 Botany
Manukau 2163
0800 BUY APCO



Surface Preparation:

Remove all dirt, dust and grease from the bare surface. If mould or fungus is present on the surface, wash it with a commercially available bleaching agent and then treat with antifungal solution. Fill cracks and imperfections with a suitable filler and spot prime. Previously painted surfaces should be sanded to remove loose/flaking paint and to reduce the previous film to a flat finish.

New Paper-faced Plasterboard: Use Acrylic Sealer Undercoat

New Woodwork, Plywood, Hardboard: Use Ezicover Acrylic Primer Undercoat or Alkyd Primer Undercoat

Aged Plaster and Plasterboard: Use Ezicover Pigmented Sealer.

Application:

Stir the contents thoroughly before and during use. Apply two liberal coats of Ezicover Ultra Low Sheen Acrylic with light sanding between coats using 220-grit sandpaper.

For Best Results:

- 1) The use of an 8 – 10mm nap roller is recommended.
- 2) Allow at least 2 hours prior to sanding & recoating.
- 3) For best results, use Ezicover Smoothcoat then Ezicover Acrylic Sealer Undercoat or Pigment Sealer before 2 top coats.
- 4) When painting over medium to dark colours, a tinted undercoat must be used for superior coverage.

Health and Safety: (Please refer to Material Safety Data Sheet before using)

Ezicover Ultra Low Sheen Acrylic is essentially non-flammable and non-hazardous.

KEEP OUT OF REACH OF CHILDREN



APCO Coatings (NZ) Ltd

14 Ron Driver Place
East Tamaki
PO Box 58849 Botany
Manukau 2163
0800 BUY APCO

V 1.2
17/04/14

Although the information and recommendations set down here in this document are presented in good faith and believed to be correct, APCO Coatings (NZ) Ltd makes no representation as to the completeness and accuracy thereof. In no event will APCO Coatings (NZ) Ltd be responsible for damages of any nature what so ever resulting from the use or reliance upon this information. No representations or warranties expressed or implied or merchantability, fitness for purpose or any other nature are made hereunder with respect to information or the product to which the information or Technical Data Sheet refers